IEC Appliance Inlet C14 with Filter, Line Switch 1- or 2-pole, Front or Rear Side Mounting







Snap-in version from front side



Screw-on mounting from front side, protection class II





70° C

See below:

Approvals and Compliances

Description

- Panel mount :
- Screw-on version from front or rear side, snap-in version front side
- 3 Functions:
- Appliance Inlet protection class I or II, Line Switch 1- or 2-pole, Line filter in standard and medical version
- Quick connect terminals 6.3 x 0.8 mm

Unique Selling Proposition

- Compact power entry module
- Available in white or black
- Switch for high inrush current
- V-Lock cord retaining

Characteristics

- Compact design with optimal shielding
- Rear side mounting for efficient costsaving assembly
- All single elements are already wired
- Line switch non-illuminated or illuminated
- Universal line filter for standard applications
- Ideal for application with high transient loads
- For applications according IEC/UL 62368-1 we recommend variants with bleed resistor

Suitable for use in medical equipment according to IEC/UL 60601-1 (1 MOOP, 1 MOPP)

Other versions on request

- Solder terminals
- Other rocker marking
- Capacitance CX1

References

Alternative: version without line filter DC11 Substitute for type KFB1; KFB2

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Detailed request for product

Newly available variants corresponding to V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.

Technical Data

Ratings IEC	1 - 10 A @ Ta 40 °C / 250 VAC; 50 Hz
Ratings UL/CSA	1 - 10 A @ Ta 40 °C / 250 VAC; 60 Hz
Leakage Current	standard < 0.5 mA (250 V / 60 Hz) medical < 5 µA (250 V / 60 Hz)
Dielectric Strength	> 1.7 kVDC between L-N > 2.7 kVDC between L/N-PE Test voltage (2 sec)
Allowable Operation Temperature	-25 °C to 85 °C
Climatic Category	25/085/21 acc. to IEC 60068-1
IP-Protection	front side IP40 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I or II acc. to IEC 61140
Terminal	Quick connect terminals 6.3 x 0.8 mm
Panel Thickness S	Screw: max 8 mm Mounting screw torque max 0.5 Nm Snap-in: 1 mm to 3 mm
Material	Thermoplastic, black / white, UL 94V-0

Appliance inlet/-outlet	C14 / C18 acc. to IEC 60320-1, UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10 A Protection Class I or II
Line Switch	Rocker switch 1-/2-pole, non-illuminated or illuminated, acc. to IEC 61058-1 Technical Details
Line Filter	Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8 Technical Details
MTBF	> 1'900'000h acc. to MIL-HB-217 F

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: DC12

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40001522
c FL °us	UL Approvals	UL	UR File Number: E72928
cac	CQC Approvals	CQC	CQC Certificate Number: CQC18001188116

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
<u>IEC</u>	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference
<u>IEC</u>	Designed according to	IEC 61058-1	Switches for appliances. Part 1. General requirements
(UL)	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
(UL)	Designed according to	UL 1283	Electromagnetic interference filters
GFA Group	Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
CSA Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Suitable for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements
<u>IEC</u>	Suitable for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance
<u>IEC</u>	Suitable for applications acc.	IEC 60335-1	Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.


Compliances

The product complies with following Guide Lines


Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
V -Lock		SCHURTER AG	V-Lock system are based on a matching plug-dose combination. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.
00	White Paper Glow wire test	SCHURTER AG	Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 &-13.
	Medical Equipment	SCHURTER AG	Suitable for use in medical equipment according to IEC/UL 60601-1 (1 MOOP, 1 MOPP)

Dimensions [mm]


Screw-on mounting from front side




Screw-on mounting from rearside (metal flange)




Snap-in mounting from front side




Screw-on mounting from front side (protection class II)



Screw-on mounting from rearside (protection class II)



Snap-in mounting from front side (protection class II)



R [**M**Ω]


Technical Da	ata of Filter-Components			
Rated Current [A]	Filter-Type	Inductances L [mH]	Capacitance CX [nF]	Capacitance CY [nF]
1	Standard version	2 x 10	100	2.2
2	Standard version	2 x 4	100	2.2
4	Standard version	2 x 1.5	100	2.2


1 Standard version 2 x 10 100 2.2 1 2 Standard version 2 x 4 100 2.2 1 4 Standard version 2 x 0.8 100 2.2 1 6 Standard version 2 x 0.8 100 2.2 1 10 Standard version 2 x 0.3 100 2.2 1 1 Medical Version (M5) 2 x 10 100 - 1 2 Medical Version (M5) 2 x 4 100 - 1 4 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M80) 2 x 0.3 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 4 Medical Version (M80) 2 x 0.8 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100						
4 Standard version 2 x 1.5 100 2.2 1 6 Standard version 2 x 0.8 100 2.2 1 10 Standard version 2 x 0.3 100 2.2 1 1 Medical Version (M5) 2 x 10 100 - 1 2 Medical Version (M5) 2 x 4 100 - 1 4 Medical Version (M5) 2 x 1.5 100 - 1 6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 1.0 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	1	Standard version	2 x 10	100	2.2	1
6 Standard version 2 x 0.8 100 2.2 1 10 Standard version 2 x 0.3 100 2.2 1 1 Medical Version (M5) 2 x 10 100 - 1 2 Medical Version (M5) 2 x 4 100 - 1 4 Medical Version (M5) 2 x 0.8 100 - 1 6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	2	Standard version	2 x 4	100	2.2	1
10 Standard version 2 x 0.3 100 2.2 1 1 Medical Version (M5) 2 x 10 100 - 1 2 Medical Version (M5) 2 x 4 100 - 1 4 Medical Version (M5) 2 x 1.5 100 - 1 6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	4	Standard version	2 x 1.5	100	2.2	1
1 Medical Version (M5) 2 x 10 100 - 1 2 Medical Version (M5) 2 x 4 100 - 1 4 Medical Version (M5) 2 x 1.5 100 - 1 6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	6	Standard version	2 x 0.8	100	2.2	1
2 Medical Version (M5) 2 x 4 100 - 1 4 Medical Version (M5) 2 x 1.5 100 - 1 6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	10	Standard version	2 x 0.3	100	2.2	1
4 Medical Version (M5) 2 x 1.5 100 - 1 6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	1	Medical Version (M5)	2 x 10	100	-	1
6 Medical Version (M5) 2 x 0.8 100 - 1 10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	2	Medical Version (M5)	2 x 4	100	-	1
10 Medical Version (M5) 2 x 0.3 100 - 1 1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	4	Medical Version (M5)	2 x 1.5	100	-	1
1 Medical Version (M80) 2 x 10 100 0.47 1 2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	6	Medical Version (M5)	2 x 0.8	100	-	1
2 Medical Version (M80) 2 x 4 100 0.47 1 4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	10	Medical Version (M5)	2 x 0.3	100	-	1
4 Medical Version (M80) 2 x 1.5 100 0.47 1 6 Medical Version (M80) 2 x 0.8 100 0.47 1	1	Medical Version (M80)	2 x 10	100	0.47	1
6 Medical Version (M80) 2 x 0.8 100 0.47 1	2	Medical Version (M80)	2 x 4	100	0.47	1
	4	Medical Version (M80)	2 x 1.5	100	0.47	1
10 Medical Version (M80) 2 x 0.3 100 0.47 1	6	Medical Version (M80)	2 x 0.8	100	0.47	1
	10	Medical Version (M80)	2 x 0.3	100	0.47	1

Diagrams

Standard filter 1-pole

Standard filter 2-pole







1) Line 2) Load 1) Line 2) Load

Medical filter 1-pole (M5)

Medical Version (M5) 2-pole







1) Line 2) Load 1) Line 2) Load

Standard filter 2-pole illuminated


Medical Filter 2-pole (M5) illuminated





1) Line 2) Load 1) Line 2) Load

Medical filter 2-pole (M5) protection class II




- 1) Line
- 2) Load

Attenuation Loss


- - - - 50Ω differential mode _____ 50Ω common mode

Standard version


1 A




2 A




4 A



6 A




10 A




Medical version (M5)


1 A




2 A




4 A



6 A



10 A



All Variants

Rated current	Filter-Type	Panel mounting	Mounting side	Line Switch	Illumination	Color	Pro- tection	V-Lock	Order Number
1	Standard version	Snap-in	Front Side	1-pole	non-illuminated	black	I	•	DC12.1102.103
2	Standard version	Snap-in	Front Side	1-pole	non-illuminated	black	I	•	DC12.2102.103
4	Standard version	Snap-in	Front Side	1-pole	non-illuminated	black	I	•	DC12.3102.103
6	Standard version	Snap-in	Front Side	1-pole	non-illuminated	black	I	•	DC12.4102.103
10	Standard version	Snap-in	Front Side	1-pole	non-illuminated	black	I	•	DC12.5102.103
1	Standard version	Snap-in	Front Side	2-pole	non-illuminated	black	I	•	DC12.1102.101
2	Standard version	Snap-in	Front Side	2-pole	non-illuminated	black	1	•	DC12.2102.101
4	Standard version	Snap-in	Front Side	2-pole	non-illuminated	black	1	•	DC12.3102.101
6	Standard version	Snap-in	Front Side	2-pole	non-illuminated	black	I	•	DC12.4102.101
10	Standard version	Snap-in	Front Side	2-pole	non-illuminated	black	I	•	DC12.5102.101
1	Standard version	Screw	Rear Side	1-pole	non-illuminated	black	I	•	DC12.1102.203
2	Standard version	Screw	Rear Side	1-pole	non-illuminated	black	I	•	DC12.2102.203
4	Standard version	Screw	Rear Side	1-pole	non-illuminated	black	I	•	DC12.3102.203

Rated current	Filter-Type	Panel mounting	Mounting side	Line Switch	Illumination	Color	Pro- tection	V-Lock	Order Number
6	Standard version	Screw	Rear Side	1-pole	non-illuminated	black	I	•	DC12.4102.203
10	Standard version	Screw	Rear Side	1-pole	non-illuminated	black	I	•	DC12.5102.203
1	Standard version	Screw	Rear Side	2-pole	non-illuminated	black	1	•	DC12.1102.201
2	Standard version	Screw	Rear Side	2-pole	non-illuminated	black	1	•	DC12.2102.201
4	Standard version	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.3102.201
6	Standard version	Screw	Rear Side	2-pole	non-illuminated	black	1	•	DC12.4102.201
10	Standard version	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.5102.201
1	Standard version	Screw	Front Side	1-pole	non-illuminated	black	1	•	DC12.1102.003
2	Standard version	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.2102.003
4	Standard version	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.3102.003
6	Standard version	Screw	Front Side	1-pole	non-illuminated	black	1	•	DC12.4102.003
10	Standard version	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.5102.003
1	Standard version	Screw	Front Side	2-pole	non-illuminated	black	I	•	DC12.1102.001
2	Standard version	Screw	Front Side	2-pole	non-illuminated	black	1	•	DC12.2102.001
4	Standard version	Screw	Front Side	2-pole	non-illuminated	black	ı	•	DC12.3102.001
6 10	Standard version	Screw Screw	Front Side Front Side	2-pole	non-illuminated	black	ı	•	DC12.4102.001 DC12.5102.001
10	Standard version Medical Version (M5)	Screw Snap-in	Front Side	2-pole 1-pole	non-illuminated non-illuminated	black black		•	DC12.5102.001 DC12.1202.103
2	Medical Version (M5)	Snap-in	Front Side	1-pole	non-illuminated	black	i i	•	DC12.2202.103
4	Medical Version (M5)	Snap-in	Front Side	1-pole	non-illuminated	black	·	•	DC12.3202.103
6	Medical Version (M5)	Snap-in	Front Side	1-pole	non-illuminated	black	' I	•	DC12.4202.103
10	Medical Version (M5)	Snap-in	Front Side	1-pole	non-illuminated	black	·	•	DC12.5202.103
	, ,	·		•				•	
6	Medical Version (M5)	Snap-in	Front Side	2-pole	illuminated green	black	1		DC12.4232.101
1	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	l "	•	DC12.1202.101
1	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	II	•	DC12.1202.121
1	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	white	II	•	DC12.1202.131
2	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	1	•	DC12.2202.101
2	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	II	•	DC12.2202.121
2	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	white	II	•	DC12.2202.131
4	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	ı	•	DC12.3202.101
4	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	II	•	DC12.3202.121
4	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	white	II	•	DC12.3202.131
6	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	I	•	DC12.4202.101
6	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	II	•	DC12.4202.121
6	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	white	II	•	DC12.4202.131
10	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	1	•	DC12.5202.101
10	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	black	II	•	DC12.5202.121
10	Medical Version (M5)	Snap-in	Front Side	2-pole	non-illuminated	white	II	•	DC12.5202.131
1	Medical Version (M5)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.1202.201
2	Medical Version (M5)	Screw	Rear Side	2-pole	non-illuminated	black	1	•	DC12.2202.201
4	Medical Version (M5)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.3202.201
6	Medical Version (M5)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.4202.201
10	Medical Version (M5)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.5202.201
1	Medical Version (M5)	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.1202.003
2	Medical Version (M5)	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.2202.003
4	Medical Version (M5)	Screw	Front Side	1-pole	non-illuminated	black	1	•	DC12.3202.003
6	Medical Version (M5)	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.4202.003
10	Medical Version (M5)	Screw	Front Side	1-pole	non-illuminated	black	I	•	DC12.5202.003
	, ,								

Rated current	Filter-Type	Panel mounting	Mounting side	Line Switch	Illumination	Color	Pro- tection	V-Lock	Order Number
1	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	1	•	DC12.1202.001
1	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	II	•	DC12.1202.021
1	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	white	II	•	DC12.1202.031
2	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	I	•	DC12.2202.001
2	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	II	•	DC12.2202.021
2	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	white	II	•	DC12.2202.031
4	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	I	•	DC12.3202.001
4	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	II	•	DC12.3202.021
4	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	white	II	•	DC12.3202.031
6	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	I	•	DC12.4202.001
6	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	II	•	DC12.4202.021
6	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	white	II	•	DC12.4202.031
10	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	I	•	DC12.5202.001
10	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	black	II	•	DC12.5202.021
10	Medical Version (M5)	Screw	Front Side	2-pole	non-illuminated	white	II	•	DC12.5202.031
1	Medical Version (M80)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.1602.201
2	Medical Version (M80)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.2602.201
4	Medical Version (M80)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.3602.201
6	Medical Version (M80)	Screw	Rear Side	2-pole	non-illuminated	black	I	•	DC12.4602.201
10	Medical Version (M80)	Screw	Rear Side	2-pole	non-illuminated	black	1	•	DC12.5602.201

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging unit

10 Pcs

Accessories

Description



Wire_Harness Wire harness for SCHURTER products



RC320 Rear Cover for Power Entry Module



Cord_retaining_kits Cord retaining strain relief

Flat head, A	4700.0001
Countersunk R	4700 0002

Mating Outlets/Connectors

Category / Description

Connector Overview complete



4782 Mounting: Power Cord, 3 x 1 mm 2 / 3 x 18 AWG, Cable, Connector: IEC C13	4782
4785 Mounting: Power Cord, 3 x 1 mm ² / 3 x 18 AWG, Cable, Connector: IEC C13	4785
4300-06 Mounting: Power Cord, 3 x 1 mm 2 / 3 x 18 AWG, Cable, Connector: IEC C13	4300-06
4781 Mounting: Power Cord, Cable, Connector: IEC C15	4781
4784 Mounting: Power Cord, 3 x 1 mm ² / 3 x 18 AWG, Cable, Connector: IEC C15	4784



Interconnection Cord Overview complete

Cord Sets 10 A, Interconnection, 1.0 m, Connector IEC C13, H05VV-F3G1.0, black	6007.0212
Cord Sets 10 A, Interconnection, 2.0 m, Connector IEC C13, H05W-F3G1.0, black	6007.0214



Power Supply Cord Overview complete

Cord Sets 10 A, Europlug, 2.0 m, Connector IEC C13, H05VV-F3G0.75, black	6004.0114	
Cord Sets 10 A, Europlug, 2.5 m, Connector IEC C13, H05VV-F3G1.0, black	6004.0215	
Cord Sets 10 A, Europlug, 2.5 m, Connector IEC C13, H05VV-F3G1.0, black	6003.0215	
Cord Sets 10 A, Europlug, Black, 2.5 m, H05W-F 3G1,0mm2, Connector IEC C13, H05W-F3G1.0, black	6004.0225	
Cord Sets 10 A, diverse, Black, 5.0 m, H05VV-F 3G1,0mm2, Connector IEC C13, H05VV-F3G1.0, black	6052.0026	

Mating Outlets/Connectors shuttered



Connector Overview complete

4783 Mounting: Power Cord. 3 x 1 mm ² / 3 x 18 AWG. Cable. Connector: IEC C13	4783



Power Cord Overview complete

VAC13KS, Overview, V-Lock cord retaining, diverse Connector IEC C13, diverse, black	VAC13KS
VAC17KS, V-Lock cord retaining, diverse m, Connector IEC C17, diverse, black / grey / white	VAC17KS

product selected for their own applications.

The specifications, descriptions and illustrations indicated in this document are based on current information. All content is subject to modifications and amendments. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability and test each